

CAPILLARY FITTINGS


Custom fittings for glass and PEEK capillaries.



The fittings for capillaries made of glass or PEEK are made to customer specifications and offer an easy option for connection with microfluidic components such as pumps and valves.

The pressure range is between -900 and 7000 mbar, with a temperature range of 5 to 60°C as standard.

By simply screwing these fittings into a female connector, capillaries can be connected to other components. We would be happy to adapt the fittings to the sizes of your capillaries.



Examples of our standard models

Product No.	Thread	Capillary Outside Diameter (O.D.)	Capillary Inner Diameter (I.D.)	Inner Diameter Seal Joint Connection
CJM4-0375	M4	0.375 mm	0.1 - 0.15 mm	0.2 mm
CJM6-1/32	M6	0.79 mm (1/32 inch)	0.3 - 0.4 mm (0.012 - 0.016 inch)	0.4 mm